

HOMEbase

20 BUBBLE BALL STRING LIGHTS

Product Specification	
Bulb Dimensions	2.5mm
Overall Wire Length	3.15m
Battery Operated	2 x AA batteries required
Light	Warm white LEDs

Contents

- 20 x bubble ball string lights.

Caution

- Do not leave used batteries for long periods in the battery compartment.
- Do not mix old and new battery types, replace all batteries at the same time.
- Remove batteries if the string lights are unlikely to be used for extended periods.

Lights

- The LEDs are a non-replaceable LED type, but have been manufactured to last for a long time.

General handling and installation





- The battery in this unit is intended for in store demonstration only. Disconnect the 'Try me' button before use.
- Handle lights with care; do not allow heavy contact with hard surfaces.
- Lights should be kept out of reach of small children and pets.
- Take care if using ladders – ensure that you have stable footing and do not over reach.

To operate

Use the slide switch at the base of the battery compartment to turn the light set ON or OFF.

Battery replacement

1. When the lights become dim, the batteries need replacing.
2. Open the battery compartment by sliding off the cover.
3. Replace all the batteries with new AA size batteries (alkaline recommended).
4. Observe the correct polarities as marked, when replacing the batteries.
5. Refit the cover.

 Recycle	<p>The packaging material is recyclable. Dispose of the packaging in an environmentally safe manner and make it available for the recyclable material collection service.</p>	
	<p>Dispose of the product in an environmentally safe manner when you decide to part with it. This device should not be disposed of with household waste. Dispose of it at a recycling centre, check with your local authority or store for recycling advice. Please note that all products with this symbol must be recycled.</p>	 light set

INSTRUCTION MANUAL

IMPORTANT: Please read these instructions before using the product and retain for future use.

HHGL Limited, MK9 1BA; HHGL (RO) Limited, DO2 X576